




Touch Side View

CONNECTOR PINOUT	
PIN#	DESIGNATION
1	Shielding
2-3	Grounding Line
4-5	Blank
6-28	X1-X23
29-33	Blank
34-50	X24-X40
51-59	Blank
60-61	Grounding Line
62	Blank
63-92	Y1-Y30
93-99	Blank
100	Grounding Line



- NOTES:
1. INPUT MODE : PROJECTED CAPACITIVE
 2. OVERALL THICKNESS : 1.75±0.20mm
 3. COVER GLASS THICKNESS : 1.10mm
 4. FRONT SURFACE : CLEAR TYPE
 5. TAIL TYPE : GOLD PLATED FPC , ZIF
 6. RECOMMENDED CONTROL BOARDS : PENMOUNT PM1400
 7. OTHER SPEC : SEE APPROVAL SHEET



NO.	DATE	DESCRIPTION	CHK
REVISION			
CHIEF OF DESIGN		APPROVED	Jerry
ENGINEER		PROJECT MANAGER	
DRAWN BY	Jerry	DATE	MAR 10 , 2011
SHT 1	OF 1	REV.	

Apex Material Technology Corp.			
TOLERANCES UNLESS SPECIFIED			
.X	± 0.50	MODEL NAME : P3009	
.XX	± 0.50	DWG NO : P3009-0-01	
.XXX	± 0.30	SCALE: N/S UNIT: mm	
ANGULAR			