



### Main

Commercial Status	Commercialised
Range of product	Harmony XB5
Bezel material	Plastic
Product or component type	Fuse carrier
Mounting diameter	22 mm

### Complementary

Product compatibility	Fuse 5 x 20 mm, 6.3 A - 250 V
Resistance to high pressure washer	7000000 Pa at 55 °C, distance: 0.1 m
Product weight	0.022 kg

### Environment

Protective treatment	TH
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Class of protection against electric shock	Class II
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK03 conforming to IEC 50102 IK03 conforming to EN 50102
Standards	EN 60947-1 EN 60947-5-1 EN 60947-5-4 JIS C 4520 UL 508 CSA C22.2 No 14
Product certifications	BV CSA DNV GL LROS (Lloyds register of shipping) RINA UL listed

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.