



ENGLISH

Datasheet

Stock No: 413-9281

RS Pro 5000m Long transparent Flexible Ducting Reinforced, 120mm Bend Radius



Product Details

PU-R Medium Weight Polyurethane Ducting

An RS Pro Brand of polyurethane (PU) hosing with a copper-plated steel spiral. Designed for suction and the transport of dusts, chips and abrasive materials.

Copper coated spring steel spiral helix between two layers of crystal clear flexible polyurethane

Excellent internal and external abrasion resistance

Retains full diameter even in tight bending radii

Suitable for the transfer of large abrasive particles such as sawdust, timber offcuts and metal swarf

Also suitable for oil and petrol fume extraction

Temperature range -40 to +90°C

Note

All data refers to performance at 18°C. Any change in temperature either above or below 18°C will affect the performance data.



Specifications

Inner Diameter	120mm
Outer Diameter	127mm
Material	PUR
Length	5000mm
Suitable Applications	Abrasive Material, Chemical, Dust, Granule, Saw Dust
Colour	Transparent
Bend Radius	120mm
Reinforced	Yes