

## TAPD58BS LF12 - Break Stem Open

| General Part Information    |                   |                                                                                   |
|-----------------------------|-------------------|-----------------------------------------------------------------------------------|
| Product Description         |                   | TAPD58BS LF12                                                                     |
| Article Number              |                   | 22237.00                                                                          |
| Rivet Type                  | <a href="#">i</a> | Break Stem Open                                                                   |
| Standard Bulk Pack Quantity |                   | 5000.00                                                                           |
| Application / Features      | <a href="#">i</a> |  |

| Geometry / Dimensions / Performance |                   |              |
|-------------------------------------|-------------------|--------------|
| Head Style                          | <a href="#">i</a> | Large Flange |
| Body Diameter Ø (mm)                |                   | 4.00         |
| Body Length (mm)                    |                   | 10.50        |
| Min. Grip Range (mm)                |                   | 4.80         |
| Max. Grip Range (mm)                |                   | 6.40         |
| Min. Hole Diameter (mm)             |                   | 4.10         |
| Max. Hole Diameter (mm)             |                   | 4.20         |
| Min. Flange Diameter (mm)           |                   | 11.50        |
| Max. Flange Diameter (mm)           |                   | 12.50        |
| Flange Thickness (mm)               |                   | 1.60         |
| Mandrel Diameter (mm)               |                   | 2.29         |
| Nominal Shear Strength (N)          |                   | 1330.00      |
| Nominal Tensile Strength (N)        |                   | 1910.00      |

| Material / Finish / Weight |                   |         |
|----------------------------|-------------------|---------|
| Body Material              | <a href="#">i</a> | AlMg3.5 |
| Mandrel Material           |                   | Steel   |
| Finish                     |                   | Clean   |
| Weight per thousand (kg)   |                   | 1.98    |

