

Device marker - US-EMSP (90X60) RD - 0802937

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Device marker, Card, red, unlabeled, can be labeled with: THERMOMARK CARD, Mounting type: Screws, rivets, Lettering field: 90 x 60 mm




The figure shows the US-EMSP (75,6x54) version

Why buy this product

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-EMSP ... UniSheet labeling range includes markers that can be attached using screws or rivets
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 881272 |
| Weight per Piece (excluding packing) | 9.99 g |
| Custom tariff number | 39204910 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|---------------|---------|
| Length (b) | 100 mm |
| Height | 0.5 mm |
| Width (a) | 60 mm |
| Hole diameter | 3.20 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 80 °C |
|---------------------------------|------------------|

Device marker - US-EMSP (90X60) RD - 0802937

Technical data

General

| | |
|---|-----------------------------|
| Color | red |
| Components | Silicone-free |
| Inflammability class according to UL 94 | V0 |
| Material | PVC |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 2 |
| Number of individual labels per row | 1 |
| Marking mounting type | Screws, rivets |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

