

7 U, 12 slot



Part no.: 20836-715

Features:

- System for horizontal board mounting at front with board format
 - Front: 6 U, 160 mm deep
- VME backplane
 - 12 slots, 6 U, J1/J2 monolithic
- Power supply unit, open frame, 444 W (400 W at < 180 VAC)
- Heat dissipation with pull-out hot-swap fan unit; filter mat; temperature-controlled by fan control module (FCM)
- Display module for DC operating voltage, fan and temperature alarm



Technical information:

Height	Height	Depth	No. of slots	Description
7 U	310.35 mm	355 mm	12	7 U, 12 slot

Delivery comprises: completely assembled, wired and tested

Item	Qty	Description
1	1	Shielded 19" chassis, Al; 19" bracket, with plain top cover and base plate (RAL 9006); front handles (RAL 7016)
2	12	Front slot; IEEE guide rails, incl. ESD clips (ESD clips fitted to right), for vertical board mounting (6 U, 160 mm deep)
3	1	VME backplane for 6 U boards, 12 slots, J1/J2 monolithic; Technical data at www.schroff.biz/oneclick enter 23001-072
4	1	Power supply unit, open frame; 444 W (400 W at < 180 V _{AC}); Technical data at www.schroff.biz/oneclick enter 11098-267
5	1	Hot-swap fan tray with 3 fans, pull-out, 1 U; Air filter; temperature-dependent speed control
6	1	Fan control module (FCM) for fan monitoring and control; technical data at www.schroff.biz/oneclick enter 23207-028
7	1	Front panel 6 U, 36 HP;
8	1	AC mains input (IEC 320-C14 plug), mains filter, mains fuse Mains switch
9	1	Rear panel, hinged, Al, 6 U, 84 HP
10	1	Cable harness to connect all system components

Note:

- Further backplanes and power supplies on request
- Please order filter mat separately
- Please order equipment cable separately
- Please order 19" case separately