

Datasheet

RS Pro Xenon V10991 Series Beacon, Red, Flashing, Surface Mount, 10 → 100 V dc

RS Stock No: **235-950**



Product Details

RS Pro multi-voltage xenon flashing beacon offers high performance with less power consumption. This weatherproof flashing beacon is suitable for battery powered vehicles such as forklift trucks. The beacon features a rugged construction with IP56 degree of protection. The beacon has an optional wire guard that is suitable for three-point mounting.

Features and Benefits

- Broad voltage range: 10 to 100 V dc
- Compact
- Low power consumption
- Rugged design, sealed to IP56
- Choose from either a 2 W or 6 W version
- Nominal flash rate: 75 fpm
- Operating temperature range: -30 to +50°C
- 130 mm high
- Optional wire guard available for the three-point mount version



ENGLISH

Specifications:

Bulb Type	Xenon
Current Type	DC
Housing Colour	Black
Lamp Included	Yes
Lens Colour	Red
Light Effect	Flashing
Special Features	Low Profile & Compact Design
Standards Met	EMC; RoHS Compliant
Base Diameter	150 mm
Current Consumption	460/395/215/130/100 mA
Height	130 mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C
IP Rating	IP56
Mounting Style	3 Point
Supply Voltage	10 to 100 V dc
Flash Rate	75 fp/min