

TIKKA® + E97 HG

Headlamp with CONSTANT LIGHTING technology for outdoor activities. **140 lumens maximum**



The TIKKA + headlamp meets the need for versatility during outdoor activities: proximity lighting, lighting for travel, Boost mode for temporary access to maximum power of **140 lumens**, red lighting and strobe mode usable at any time to signal one's presence. The headlamp features CONSTANT LIGHTING technology: brightness does not decrease gradually as the batteries are drained.

Description

- CONSTANT LIGHTING: brightness does not decrease gradually as the batteries are drained
- Several modes and lighting colors adapt to each situation:
 - ambient mode: wide beam with reduced brightness, avoids blinding others in a group situation and provides a long burn time
 - a mode adapted for close range vision: mixed beam with wide, uniform flood
 - a mode adapted for movement: mixed beam with focused component allows user to move around comfortably
 - Boost mode for temporary access to maximum power
 - red lighting for discreet close range vision
 - strobe mode for signaling one's presence, accessible at any time
- Burn time management allows user to easily anticipate battery replacement:
 - automatically switches to reserve mode when batteries are almost drained (signaled by blinking light)
 - red lighting switches on when batteries are practically empty to preserve maximum visibility
 - by using Ni-MH or lithium batteries you can double the burn time while keeping the same brightness
- Easy to use:
 - push-button is easy to use, even with gloves
 - mixed fabric and elastic headband for improved comfort and support during dynamic activities
 - washable headband
 - battery case opens easily for changing batteries

Specifications

- Weight: 85 g
- Technology: CONSTANT LIGHTING
- Beam pattern: mixed
- Energy: 3 AAA/LR03 batteries (included)
- Battery compatibility: rechargeable Ni-MH and lithium
- Certification(s): CE
- Watertightness: IP X4 (weather resistant)
- Colour grey