

Datasheet

RS Pro 127 x 47 x 93.5mm Inspection Window For Use With 46277-3, DIN 43880

RS Stock No: **297-1235**



Product Details

RS Pro inspection window in grey colour, is made from polycarbonate measures of 127 x 24 x 93.5 mm and has IP67 IP rating. It is suitable for use with 46277-3, DIN 43880.

Features and Benefits

- IP67 rated
- Polycarbonate inspection windows in smoked grey for 2, 6, 8 and 12 modules
- Breakaway finger protection panel, suitable for DIN 43880/46277-3 cases
- Windows are spring-loaded and can be secured with thumb screws
- Temperature range from -25 to +80°C

Specifications:

Colour	Grey
Dimensions	127 x 47 x 93.5 mm
For Use With	DIN 43880, DIN 46277-3
Height	93.5 mm
Length	127 mm
Material	PC
Type	Inspection Window
Width	47 mm
IP Rating	IP67, IP44
Temperature Rating	-25 to +80°C

