







DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



WIRE RANGE : 0,75-1,50 mm² (18-16 AWG)
INSUL. RANGE : 2,0 -2,5 mm (.080-.100)

DIRECTION OFF TOP OF REEL	
AMPOMATOR + MINI-APPL. 107-3-F16.1	A
107-3-F16.2	B
107-3-F16.4	C

5-163081-3	A		BRASS	ECON. GOLD	21
5-163081-2	A		BRASS	SEL. GOLD	22
5-163081-1	A		BRASS	EL. TIN	20
1-163081-8	A	1-163082-8	BRASS	TIN/LEAD	30
1-163081-7	A		BRASS	SILVER	28
1-163081-6	B	1-163082-6	BRASS	SILVER	28
1-163081-5	A		PH. BRONZE	PRE-TIN	
1-163081-4	B		PH. BRONZE	PRE-TIN	
1-163081-3	A		BRASS	PRE-TIN	
1-163081-2	B		BRASS	PRE-TIN	
1-163081-1	A	1-163082-0	BRASS	ECON. GOLD	21
1-163081-0	B		BRASS	ECON. GOLD	21
163081-9	A	1-163082-1	BRASS	EL. TIN	31 20
163081-8	A		BRASS	EL. TIN	20
163081-7	A		BRASS	SEL. GOLD	22
163081-2	A	163082-2	BRASS	SEL. GOLD	22
163081-1	A	163082-1	BRASS	EL. TIN	20

NOTES	MATERIAL	THICKNESS	AREA
21	TIN	2,0 μm	ALL OVER
22	NICKEL GOLD TIN/LEAD	0,8 μm	ALL OVER CONTACT AREA BARREL
23	NICKEL GOLD GOLD	0,8 μm	ALL OVER CONTACT AREA ALL OVER
24	NICKEL GOLD GOLD	1,2 μm	ALL OVER CONTACT AREA ALL OVER
25	NICKEL SILVER TIN/LEAD	2,5 μm	ALL OVER CONTACT AREA BARREL
26	SILVER NICKEL	1,5-2,5 μm 0,76 μm	ALL OVER ALL OVER
29	SILVER	2,5 μm	ALL OVER
30	NICKEL	1,27 μm	ALL OVER
31	TIN/LEAD	1,27 μm	ALL OVER
32	LUBRICATED		

REVISION RECORD			
LTR.	DATE	CHK.	DATE
AW	EBD0-0335-04	JMS	FWK 02-08-04
W	EH-1347-96	JvL	RV 21-11-96
V	EH-0302-94	JvL	MvD 03-05-94
U	ECN H-9813	JvdH	RD 18-05-92
T	ECN H-9192	MvD	RD 09-10-91
DR.		APP.	
DATE		DATE	

CUSTOMER DRAWING FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION 19

AMP AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

PIN TYPE III CONTACT
SIZE 16

DWG. No. 163081 REV. LTR. SHEET 1 OF 1 A3

- NOTES :
- 1 U.L. RECOGNIZED UNDER FILE E28476 VOL. VI SEC. I.
 - 2 FOR CRIMP DETAILS SEE AMP-SPEC. 114-19.000.
 - 3 MEETS PRODUCT SPECIFICATION 108-10042.
 - 4 0,40 MAX. GAP BETWEEN SPRING-NOSE AND CONTACT BODY.
 - 5 SPECIAL REEL WITH 200 PCS FOR REEL-FED HANDTOOL.