

Plate Switches

Chrome and Satin Chrome



Description

The elegantly styled Deta Decorative range is easy to install, with coloured terminals, clear white terminal markings and is supplied in individual display boxes.

Features

- black or white inserts available
- metal capped rocker versions
- only one size 4mm screwdriver needed
- x-rated and can be used for switching inductive or fluorescent loads without de-rating
- clear white terminal markings
- captive and backed out terminals
- terminals have large lead-ins
- range can be expanded using Gridswitch range
- 25 year guarantee

Range

plastic switch rockers

10A 1g 2way	1903
10A 2g 2way	1904
10A 3g 2way	1905
10A 4g 2way	1920
10A intermediate	1946
10A 3 pole fan isolator	1949

metal capped switch rockers

10A 1g 2way	2903
10A 2g 2way	2904
10A 3g 2way	2905
10A 4g 2way	2920
10A intermediate	2946
10A 3 pole fan isolator	2949

prefix with finish

chrome	CH
satin Chrome	SC
white or black inserts	W or B

Technical Specification

voltage rating	250Vac
current rating	10A
	X rated
contact gap	3mm

no user serviceable parts

Back Boxes

minimum recommended depth

	flush 25mm	dry lining 35mm
1-3g	DB162	DB2540
4g	DB163	DB2541

Standards

- BS EN 60669-1:2000

Terminal Capacity

	1mm ²	1.5mm ²	2.5mm ²	4mm ²
L	5	4	2	1

DETA

Kingsway House, Laporte Way
Luton, Beds LU4 8RJ

Tel. +44 1582 544 500 Fax: +44 1582 544 501
Technical Helpline +44 1582 544 548