



Datasheet

Stock No: 545-109

ENGLISH

RS Pro Bending, Cutting Hand-Held Tool



Product Details

Component Lead Forming Tools - Crop & Bend

A high quality, lightweight hand tool, similar to component lead bending tool 545-086 but having the additional facility of cropping the leads to a desired length. Both operations (cropping and bending) are carried out simultaneously and the length of cut each side is independently adjustable. Overall dimensions (mm): W. 76 H. 145 D. 140

Key Characteristics

Lead diameter capacity	0.25 - 1 mm
Max. length of bend	16 mm
Min. length of bend	6.5 mm
Max. length of cut	32 mm
Min. length of cut	16 mm
Min. distance of bend from of component	1 mm
Max. component body diameter	13 mm



ENGLISH

Specifications:

Task Type	Bending, Cutting
Tool Type	Hand-Held Tool
Maximum Bend Length	16mm
Maximum Cut Length	32mm
Maximum Lead Diameter Capacity	1mm
Minimum Bend Length	6.5mm
Minimum Cut Length	16mm
Minimum Lead Diameter Capacity	0.25mm
Bend Length Range	6.5 → 16mm
Lead Diameter Capacity Range	0.25 → 1mm
Cut Length Range	16 → 32mm