
ITT 1000 W 235 V-08X0

HALOTHERM | Infrared halogen lamps with white reflector



Areas of application

- Manufacture of PET bottles
- Coil coating
- Professional grills and heated counters in restaurants

Product benefits

- High efficiency
- Precise controllability
- Long lamp life
- Short response time



Product datasheet

Technical data

Electrical data

Nominal wattage	1000.00 W
Nominal voltage	235 V
Nominal current	4.3 A
Lamp current	4.30000 A
Construction voltage	235 V

Photometrical data

Color temperature	2350 K
-------------------	--------

Dimensions & weight



Diameter	10.0 mm
Length	365.0 mm
Filament length	270.00 mm

Lifespan

Lifespan	5000 h
----------	--------

Additional product data

Base (standard designation)	X ¹⁾
-----------------------------	-----------------

¹⁾ Metal strip connection according to EN 60240-1

Capabilities

Burning position	p15
------------------	-----

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
--------------	------------	---------	------------	--------

Product datasheet

4008321555113	OSRHALOTT10008X0	-	-	-
---------------	------------------	---	---	---

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321555113	ITT 1000 W 235 V-08X0	Role 1	45 mm x 42 mm x 645 mm	1.22 dm ³	185.00 g
4008321555120	ITT 1000 W 235 V-08X0	Shipping carton box 12	150 mm x 190 mm x 660 mm	18.81 dm ³	2420.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.