



iM2306 Medium Case



Two Press & Pull Latches

- Two Press & Pull Latches
- Double-layered, Soft-grip Handle
- Two Padlockable Hasps
- Vortex® Valve
- Flush Powerful Hinges
- Meets airline regulations for carry-on luggage*
- **Meets airline regulations for carry-on luggage***
- Lightweight Strong HPX® Resin
- Watertight
- Dustproof
- *Check with your airline for exact measurement requirements
- **Where applicable by law

CONFIGURATIONS

- iM2306 - Standard
- iM2306-X0000 - With No Foam
- iM2306-X0002 - With With Padded Dividers

DIMENSIONS

- Interior (L x W x D):** 17.00 x 6.30" x 6.20 (43.2 x 16 x 15.7 cm)
- Exterior (L x W x D):** 18.20 x 8.40" x 6.70 (46.2 x 21.3 x 17 cm)
- Lid Depth:** 2.00"
- Bottom Depth:** 4.20"
- Total Depth:** 6.2"
- Int Volume:** 0.38 ft³

MATERIALS

- Body:** Injection Molded HPX® high performance resin
- Latch:** Valox - Polybutylene Terephthalate (PBT)
- Latch (Alt):** Xenoy - Polyester/Polycarbonate blend
- O-Ring:** Silicone Sponge
- Pins:** Stainless Steel
- Pins (Alt):** Aluminum
- Foam:** 1.3/1.35 polyester
- Purge Body:** Valox - Polybutylene Terephthalate (PBT)
- Purge Body (Alt):** Xenoy - Polyester/Polycarbonate blend

Purge Vent: Gortex membrane

Purge O-Ring: Buna-N, 50-60 Durometer Shore A

COLOURS



Black



OD Green

WEIGHT

Weight With Foam: 4.70 lbs

Weight Without Foam: 4.30 lbs

Buoyancy: 24.25 lbs

Master Pack Weight: 29.00 lbs

TEMPERATURE

Minimum Temperature: -20°

Maximum Temperature: 140°

CERTIFICATIONS

MIL-STD-810F

ATA 300

FED-STD-101C

FOAM PROPERTIES

Layer 1 (Lid): 2.00" Convolute

Layer 2 (Base): 0.63" Pad

Layer 3 (Base): 1.81" Pick N Pluck

Layer 4 (Base): 1.81" Pick N Pluck

OTHER

Master Pack: 4

Military: yes

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com