

87 26 250

KNIPEX Cobra® VDE Hightech Water Pump Pliers, insulated



- adjustment by shifting one jaw directly on to the workpiece: fast, reliable and comfortable handling
- opening at the touch of a button apart from the workpiece
- fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- good access to the workpiece due to slim size of head and joint area
- self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- box-joint design: high stability due to double guide
- guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, oil-hardened

The adjustment action to adapt to the workpiece is easy and reliable with the KNIPEX Cobra® VDE: place the upper gripping jaw of the opened pliers on the workpiece, push pliers to close, done!

Article No.	87 26 250
EAN	4003773071495
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Head	
Insulation standard	IEC 60900 DIN EN 60900
Adjustment positions	24
Capacities for pipes Ø Inch	2
Capacities for nuts mm	46
Capacities for pipes Ø mm	50
Length mm	250
Net weight g	340



technical change and errors excepted



Spare Parts

Article No.	EAN	
87 29 250		Range of spare parts adjustment for 87 2. 250