



- Rework - Soldering, Desoldering and Hot Air
- Power unit, 3 channels with WXHAP 200 Hot air iron, WXDP 120 Desoldering iron and WXP 120 Soldering iron

### WXR 3031

Code No.: T0053502699

Dimensions W x D x H (mm)	273 x 235 x 102
Dimensions W x D x H (Inch)	10,75 x 9,25 x 4,02
Weight (ca) in kg	6,7 kg
Voltage	230 V (50/60 Hz)
Power output	420 W (600 W)
Channels	3
Temperature range (depends on tool) °C	100 - 450 (550)
Temperature range (depends on tool) °F	200 - 850 (999)
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding	Via 3.5 mm pawl socket on back of device (Hard grounded)
Display	255 x 128 dots / Backlighting
Air consumption l/min	---
Operating pressure	---
Capacity l/min	18
Vacuum	---