

## Housing - VC-MP-T2-R-M25 - 1886647

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Powder-coated sleeve housing, with metric cable entry, locking screws with knurled head



### Key commercial data

Packing unit	5 pc
GTIN	 4 017918 848064
Weight per Piece (excluding packing)	255.93 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Height	65 mm
Width	33 mm
Length	74 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### General

Note	When using fiber optics, the bending radii of the cable manufacturers must be observed.
Type	VC2
Housing type	Sleeve housings
Color	gray
Locking type	Screw locking, knurled head
Tightening torque, mounting screw	1.5 Nm ±0.3 Nm
No. of cable exits	1
Cable exit	Angled
Screw connection	None

# Housing - VC-MP-T2-R-M25 - 1886647

## Technical data

### General

Type of the screw connection	M25
Housing material	Zinc die-cast
Housing surface material	Powder coating
Seal material	EPDM
Material of locking screw	Nickel-plated brass

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27371205
eCl@ss 5.1	27371205
eCl@ss 6.0	27371205
eCl@ss 7.0	27371205
eCl@ss 8.0	27371205

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Accessories

### Accessories

Marking label - VC-BZS WH - 1852875



Marker labels, unprinted, 5-section, for individual labeling with M-PEN or CMS system, white

## Drawings

## Housing - VC-MP-T2-R-M25 - 1886647

Dimensioned drawing

