

DIN rail - NS 30/15 PERF.2000MM - 3240262

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




DIN rails, for accommodating cable clamps

Why buy this product

- ✓ If you require greater quantities, the same article is available in a unit pack of 25 pcs. (50 m)
- ✓ Individual or bundled cables with a diameter of up to 64 mm can be installed safely and easily
- ✓ The halogen-free plastic troughs have been designed to be perfectly secure while simultaneously protecting the conductors
- ✓ The cable clamps provide strain relief



Key commercial data

Packing unit	5 pc
GTIN	 4 046356 480833
Weight per Piece (excluding packing)	1400.0 g
Custom tariff number	72166190
Country of origin	Germany

Technical data

Dimensions

Height	15 mm
Length	2000 mm
Width	30 mm

General

Material	Steel
Coating	Galvanized
Test standard	In acc. with EN 60715: 2001

DIN rail - NS 30/15 PERF.2000MM - 3240262

Classifications

eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27141143
eCl@ss 7.0	27141143
eCl@ss 8.0	27141143

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Dimensioned drawing

