

Heat & Cold Resistant

Print date 05-08-2014

Glove material

- N/A (Coating material)
- Spandex (Liner material)
- Acrylic (Liner material)

Possible Harmful ingredients**Sensitizers**

- No sensitizers

Reach Regulation 1907/2006

For more information, please consult the REACH statement on the Ansell website

Properties

- Good dexterity
- Good dry grip

EN Test Data**Abrasion resistance:**

Performance level 1

Blade cut resistance:

Performance level 1

Tear resistance:

Performance level 3

Puncture resistance:

Performance level X

Convective cold:Performance level 0 Thermal Insulation $I_{tr} < 0.10 \text{ m}^2 \cdot \text{C}/\text{w}$ **Contact cold:**Performance level 1 Thermal Resistance $R > 0.025 \text{ m}^2 \cdot \text{C}/\text{w}$ **Water resistance:**

Performance level 0 water permeation

European conformity

Gloves conform to the requirements of the European Directive 89/686/EEC and to the European standards EN 420:2003 + A1:2009 and EN 388:2003

They are categorised in "Intermediate Design" (= Protection against intermediate risks).

EC-Type Examination Certificate for the final product by
Centexbel
Technologiepark 7
B-9052 Zwijnaarde

Gloves conform to the requirements of the European Regulation 1935/2004 "Materials and Articles to Come into Contact with Foodstuff" and European Regulation 2023/2006 "Good Manufacturing Practices for Materials and Articles to Come into Contact with Foodstuffs".

For more information on food compliance, please consult Ansell Food Declaration of Product Compliance.

Application - Limitations of use

Hand protection - light duty applications.

Do not use against flames nor temperatures of $> 70^\circ\text{C}$

Do not use against chemicals; the glove is not liquidproof

Storage

Keep away from sources of ozone or ignition.

Keep out of direct sunlight; store in a cool and dry place.

Construction	Gauge	Liner material	Finishing	Coating material	Cuff style	Colour	EN Size	Length mm	Packaging
Knitted	10	Spandex Acrylic	-	N/A	Knitwrist	Blue	7, 9	230, 260	1 pair in a bag; 144 pairs in a carton

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

http://www.ansell.eu • E-mail info@ansell.eu