



ENGLISH

Datasheet

RS Pro Dial Thermometer, Centigrade, Fahrenheit Scale, -35 to +55 °C, 30cm dia. Wall Mount

RS Stock No: **828-763**



Product Details

RS Pro dial thermometer is a large wall mounting thermometer that comes with a stainless steel spring movement capable of reading -35 to +55°C (30 to 130°F) with an accuracy of $\pm 1^{\circ}\text{C}$. It is suitable for factories and offices.

Features and Benefits

- Large wall mounting thermometer
- Stainless steel spring movement capable of reading -35 to +55°C (30 to 130°F) with an accuracy of $\pm 1^{\circ}\text{C}$
- Suitable for factories and offices



Specifications:

Application	Factory, Office
Best Accuracy	±1°C
Dial Diameter	12 in
Maximum Temperature Measurement	+55°C
Temperature Scale	Centigrade, Fahrenheit
Thermometer Type	Wall Mount
Temperature Range	-35 to +55°C