

Datasheet

## RS Pro Straight 50Ω Panel Mount TNC Connector, jack, Solder Termination

RS Stock No: 793-3626



### Product Details

RS Pro panel mount TNC connector jack is designed for 50 Ω impedance applications. This straight connector jack offers solder termination. The waterproof, coaxial clamp jack comes with complete IP68 sealing against gas and moisture ingress along the whole connector. This bulkhead clamp jack has a nickel plated brass body, PTFE insulator, silicone 'O' rings and a gold plated centre contact.

### Features and Benefits

- Nominal impedance 50Ω
- Gold-plated contacts
- Solder termination



ENGLISH

### Specifications:

Body Orientation	Straight
Body Plating	White Bronze
Contact Material	Gold
Contact Plating	Beryllium Copper
Gender	Female
Impedance	50 $\Omega$
Mounting Type	Panel Mount
Operating Frequency	0 to 11 GHz
Termination Method	Solder
Dimensions	31.37 x 14.5 mm
Operating Temperature Range	-65 to +165°C