


KEMET Part Number: LDEMG3220JA5N00
(DEMG3220JA5N00)

LDE, Film, Metallized PEN Stacked, Automotive Grade, 0.22 uF, 5%, 160 VAC, 400 VDC, 125°C, 5040, 3.8mm



General Information

Supplier:	KEMET
Series:	LDE
Dielectric:	Metallized PEN Stacked
Style:	SMD Chip
Features:	Automotive Grade
RoHS:	Yes
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Shelf Life:	104 Weeks
MSL:	2

Dimensions

Chip Size	5040
L	13mm +/-0.4mm
W	10.4mm +/-0.5mm
T	3.8mm MAX
B	0.5mm +/-0.5/-0.3mm

Packaging Specifications

Packaging:	T&R
Packaging Quantity:	1250

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage AC:	160 VAC
Voltage DC:	400 VDC
Temperature Range:	-55/+125C
Rated Temperature:	125°C
Dissipation Factor:	0.80% 1kHz
Insulation Resistance:	1 GOhms
Max dV/dt:	100 V/us