


| NO | DESCRIPTION                                              | DATE      |
|----|----------------------------------------------------------|-----------|
| ①  | DEL PROOF VOLTAGE<br>WORKING VOLTAGE<br>→ VOLTAGE RATING | 07.16.14' |



## 1.3 MAX. @ 7.5GHz

**5.1 OPERATING TEMPERATURE RANGE: -55° C TO +155° C**

|    |                |                  |      |                        |
|----|----------------|------------------|------|------------------------|
| 5  | O-RING         | SILICONE         | 1    | BLACK                  |
| 4  | INSULATION     | TEFLON           | 1    | NONE                   |
| 3  | BODY           | BRASS            | 1    | WHITE BRONZE 80μ" MIN. |
| 2  | CHASSIS        | BRASS            | 1    | WHITE BRONZE 80μ" MIN. |
| 1  | CENTER CONTACT | BERYLLIUM COPPER | 1    | SILVER 70μ" MIN.       |
| NO | DESCRIPTION    | MATERIAL         | Q'TY | FINISH                 |



|             |          |                                                                         |       |       |                      |         |        |         |    |           |    |      |
|-------------|----------|-------------------------------------------------------------------------|-------|-------|----------------------|---------|--------|---------|----|-----------|----|------|
| DESCRIPTION |          | LOW PIM STRAIGHT SQUARE FLANGE MOUNT FIELD THROUGH 7/16 JACK RECEPTACLE |       |       |                      |         |        |         |    |           |    |      |
| 製圖          | DRAWN    | TOLERANCE                                                               |       | 品名    | 62-17                |         | T.S.WB |         | 日期 | DATE      | 版次 | REV. |
|             | Kristina | X                                                                       | ±0.2  | TITLE | ROHS COMPLIANT (50n) |         |        |         |    | 02.09.12' |    | A-1  |
| 檢圖          | CHECK    | XX                                                                      | ±0.1  | 單位    | UNIT                 | DWG.NO. |        | 62-0003 |    |           |    |      |
|             | Arc      |                                                                         |       |       | mm(in)               |         |        |         |    |           |    |      |
| 認定          | APPROVAL | XXX                                                                     | ±0.05 | 比例    | SCALE                |         |        |         |    |           |    |      |
|             | Angela   | ANGLE                                                                   | ±5°   |       | 3:1                  |         |        |         |    |           |    |      |