










C_Tape_tape

Raychem Electrical PVC Tape

TE provides multiple grades of tape that provide UV resistance, flame retardant, cold weather performance while meeting cost effective solutions.

Professional grade tapes are used for electrical insulation of joints and splices in wires and cables up to 600 Volts. Commercial grade and General Purpose tapes are utilized for wrapping wire harnesses and insulating degaussing coils as well as being used as a protective jacket. Electrical phases, circuits, feeders and branches can be easily identified by our colored line of PVC tapes.

Part Number	Description	Mil Thickness
3030	 All Weather, PVC black pressure sensitive tape. Weather resistant, flame retardant, lead-free. Primary insulation for splices up to 600 V and all low temperature applications.	7 mil (0.18 mm)
8080	 Professional grade, PVC pressure sensitive, all weather vinyl tape, highly elastic and heavier thickness for added mechanical and electrical protection. Cold and weather resistant, flame retardant and lead-free. Primary insulation for splices at not more than 600 V and excellent protective jacket over all types of splices. Excellent cold weather performance.	8.5 mil (0.21 mm)
7070	 Professional grade, PVC pressure sensitive, all weather vinyl tape that is available in nine fade resistance colors for coding and insulating. Flame retardant and lead-free. Used for quick identification and/or a warning signal of electrical circuits, containers, and conduit system, as well as primary insulation for splices at not more than 600 V. Available colors: red, blue, yellow, green, white, orange, brown, violet, white.	7 mil (0.18 mm)
4040	 Commercial grade, PVC pressure sensitive, all weather vinyl tape that provides heavier thickness for added mechanical and electrical protection. Cold and weather resistant, flame retardant and lead-free. Can be used as primary insulation for splices at not more than 600 V and excellent protective jacket over all types of splices. Excellent cold weather performance.	8.5 mil (0.21 mm)
2020	 Heavy Duty, PVC pressure sensitive vinyl tape giving complete environmental mechanical and electrical protection for all types of pipewrapping applications. UV, bacteria and fungus resistant. Lead-free and flame retardant. Can be used for overhead and direct burial applications.	10 mil (0.25 mm)
5050	 Commercial grade, PVC pressure sensitive vinyl tape for general electrical insulation purposes. Insulate and repair for mining applications. Flame retardant, weather resistant and lead-free. Can be used for splices not more than 600 V.	7 mil (0.18 mm)
1818	 General Purpose, PVC pressure sensitive vinyl tape for general electrical insulation purposes. Flame retardant, weather resistant and lead-free. Can be used for splices not more than 600 V. Available in nine fade resistant colors: red, blue, yellow, green, white, orange, brown, violet, white, black.	7 mil (0.18 mm)

Selection Information:

Product Description	Catalog Number	Color	Thickness mil (mm)	Roll Width inches (mm)	Roll Length yard/feet (m)	Package Type	
2020	ETP-2020-0-25-33-B	Black	10 (0.25)	1 (25.4)	36 yd (32.9)	Cellophane	
	ETP-2020-0-51-33-B	Black	10 (0.25)	2 (51.4)	36 yd (32.9)	Cellophane	
	ETP-2020-0-38-33-B	Black	10 (0.25)	1-1/2 (38)	36 yd (32.9)	Cellophane	
	ETP-2020-0-19-33-B	Black	10 (0.25)	3/4 (19)	36 yd (32.9)	Cellophane	
3030	ETP-3030-0-19-20-A	Black	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-3030-0-19-20-P-A	Black	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
7070	ETP-7070-5-19-20-P-A	Green	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-4-19-20-P-A	Yellow	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-2-19-20-P-A	Red	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-6-19-20-P-A	Blue	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-9-19-20-P-A	White	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-1-19-20-P-A	Brown	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-3-19-20-P-A	Orange	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-8-19-20-P-A	Gray	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-7-19-20-P-A	Violet	7 (0.18)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-7070-6-13-06-B	Blue	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-3-13-06-B	Orange	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-2-13-06-B	Red	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-9-13-06-B	White	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-4-13-06-B	Yellow	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-8-13-06-B	Gray	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-5-13-06-A	Green	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-7-13-06-A	Violet	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	ETP-7070-1-13-06-A	Brown	7 (0.18)	1/2 (13)	20 (6.1)	Cellophane	
	4040	ETP-4040-0-19-20-B	Black	8.5 (0.21)	3/4 (19)	66 (20.1)	Cellophane
		ETP-4040-0-25-20-B	Black	8.5 (0.21)	1 (25.4)	66 (20.1)	Cellophane
ETP-4040-0-38-20-A		Black	8.5 (0.21)	1-1/2 (38)	66 (20.1)	Cellophane	
ETP-4040-0-38-20-B		Black	8.5 (0.21)	1-1/2 (38)	66 (20.1)	Cellophane	
ETP-4040-0-51-20-B		Black	8.5 (0.21)	2 (51.4)	66 (20.1)	Cellophane	
8080	ETP-8080-0-19-20-A	Black	8.5 (0.21)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-8080-0-19-20-P-A	Black	8.5 (0.21)	3/4 (19)	66 (20.1)	Plastic Case	
	ETP-8080-0-25-20-B	Black	8.5 (0.21)	1 (25.4)	66 (20.1)	Cellophane	
	ETP-8080-0-25-20-A	Black	8.5 (0.21)	1 (25.4)	66 (20.1)	Cellophane	
	ETP-8080-0-38-20-B	Black	8.5 (0.21)	1 1/2 (38)	66 (20.1)	Cellophane	
1818	ETP-1818-0-19-20-B	Black	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-5-19-20-B	Green	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-4-19-20-B	Yellow	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-2-19-20-B	Red	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-6-19-20-B	Blue	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-9-19-20-B	White	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-1-19-20-B	Brown	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-3-19-20-B	Orange	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
	ETP-1818-8-19-20-B	Gray	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	
ETP-1818-7-19-20-B	Violet	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane		
5050	ETP-5050-0-19-20-B	Black	7 (0.18)	3/4 (19)	66 (20.1)	Cellophane	

Note: A = 1 inch core, B = 1-1/2 inch core

For additional parts contact your local TE representative.