



Product Information

2444DIK125R26-28D

Swivel castor with central, total or directional lock, housing made of pressed steel, zinc-chromatised, covered precision swivel bearing, hardened balls and tracks, bearing sleeve welded to fork, wheel axle with nut.

Wheel centre made of pressed steel, Tread: solid rubber, grey non-marking with threadguards, cone ball bearing, stem with cam hole for profile bars.

Wheel diameter	125 mm
Tread width	32 mm
Hardness of tread	Shore D 40
Bolt-Ø	28 mm
Bolt length	96 mm
Offset	43 mm
Overall height	168.5 mm
Temperature	-40 / +80 °C
Standard	EN 12530
Dynamic load capacity	100 kg
Static load capacity	200 kg