

Datasheet

RS Pro Straight 75Ω Cable Mount BNC Connector Plug, Clamp Termination URM 202

RS Stock No: **546-4314**



Product Details

RS Pro cable mount BNC connector plug has a nickel plated body, gold plated centre contact and is suitable for URM 202 cables. This 75 Ω straight BNC connector plug comes with bayonet coupling and a cable clamp termination. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body
- Gold plated centre contacts
- Clamp termination method

Specifications:

Body Orientation	Straight
Body Plating	Silver
Cable Type	URM 202
Contact Material	Copper
Contact Plating	Silver
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Operating Frequency	1 GHz
Polarity	Normal
Termination Method	Clamp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-65 to +165°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)
VSWR (Voltage Standing Wave Ratio)	1.3