

Datasheet

## RS Pro Swivel Plate Castor, 120kg

RS Stock No: **420-3887**



### Product Details

RS Pro swivel castor has load capacity of 120 kg. This high temperature thermoplastic castor features phenolic resin hub for a strong and easy roll.

### Features and Benefits

- Very wide operating temperature range of -70 to +280°C
- Available in fixed, swivel and braked swivel versions
- Fixing centres 80 x 60 mm
- Fixing holes M8 clearance



ENGLISH

## Specifications:

Features	High Temperature
Fixing Centres (Length)	80 mm
Fixing Centres (Width)	60 mm
Fixing Centres	80 x 60 mm
Fixing Hole Size	8 mm
Fixing Plate Dimensions	100 x 80 mm
Fixing Plate Length	100 mm
Fixing Plate Width	80 mm
Hub Material	Phenolic Resin
Includes Brake	Yes
Load Capacity	120 kg
Number of Fixing Holes	4
Overall Height	123 mm
Rotation	Swivel
Tyre Material	Phenolic
Wheel Diameter	100 mm