


Selection guide

Steel wall-mounting enclosures

PE60010B-15



PE60010C-12



Specifications						Spacial CRN - CRNG			
Dimensions			No. of doors	IP	Weight (1)	Plain door with mounting plate	Plain door without mounting plate	Glazed door without mounting plate	
H	W	D				Page 48			
CRN Wall-mounting steel enclosures									
200	200	150	1	66	2.5	-	NSYCRN22150 (2)	-	
	300	150	1	66	3.9	-	NSYCRN23150 (2)	-	
250	200	150	1	66	3.2	NSYCRN252150P	NSYCRN252150	-	
300	250	150	1	66	4.2	NSYCRN325150P	NSYCRN325150	NSYCRN325150T	
		200	1	66	4.9	NSYCRN325200P	NSYCRN325200	NSYCRN325200T	
300	300	150	1	66	5.0	NSYCRN33150P	NSYCRN33150	NSYCRN33150T	
		200	1	66	6.0	NSYCRN33200P	NSYCRN33200	NSYCRN33200T	
		400	1	66	6.4	-	NSYCRN34200	NSYCRN34200T	
400	450	150	1	66	6.7	-	NSYCRN345150 (2)	-	
		300	150	1	66	6.0	NSYCRN43150P	NSYCRN43150	NSYCRN43150T
			200	1	66	6.8	NSYCRN43200P	NSYCRN43200	NSYCRN43200T
		400	1	66	8.0	NSYCRN44200P	NSYCRN44200	NSYCRN44200T	
		600	1	66	10.0	NSYCRN46250P	NSYCRN46250	NSYCRN46250T	
500	400	300	1	66	11.2	NSYCRN46300P	NSYCRN46300	NSYCRN46300T	
		150	1	66	8.7	NSYCRN54150P	NSYCRN54150	NSYCRN54150T	
			200	1	66	9.8	NSYCRN54200P	NSYCRN54200	NSYCRN54200T
			250	1	66	11.0	NSYCRN54250P	NSYCRN54250	NSYCRN54250T
		500	1	66	12.8	NSYCRN55250P	NSYCRN55250	NSYCRN55250T	
600	400	150	1	66	9.3	NSYCRN64150P	NSYCRN64150	NSYCRN64150T	
		200	1	66	10.8	NSYCRN64200P	NSYCRN64200	NSYCRN64200T	
		250	1	66	12.3	NSYCRN64250P	NSYCRN64250	NSYCRN64250T	
	500	150	1	66	11.3	NSYCRN65150P	NSYCRN65150	NSYCRN65150T	
		200	1	66	14.3	NSYCRN65200P	NSYCRN65200	NSYCRN65200T	
		250	1	66	16.2	NSYCRN65250P	NSYCRN65250	NSYCRN65250T	
	600	200	1	66	16.3	-	NSYCRN66200	NSYCRN66200T	
			1	66	18.2	NSYCRN66250P	NSYCRN66250	NSYCRN66250T	
		300	1	66	19.8	NSYCRN66300P	NSYCRN66300	NSYCRN66300T	
			1	66	26.0	-	NSYCRN68300	NSYCRN68300T	
700	500	200	1	66	17.3	NSYCRN75200P	NSYCRN75200	NSYCRN75200T	
		250	1	66	19.3	NSYCRN75250P	NSYCRN75250	NSYCRN75250T	
800	600	200	1	66	21.8	NSYCRN86200P	NSYCRN86200	NSYCRN86200T	
		250	1	66	24.8	NSYCRN86250P	NSYCRN86250	NSYCRN86250T	
		300	1	66	26.3	NSYCRN86300P	NSYCRN86300	NSYCRN86300T	
	800	200	1	66	29.5	NSYCRN88200P	NSYCRN88200	NSYCRN88200T	
		300	1	66	32.5	NSYCRN88300P	NSYCRN88300	NSYCRN88300T	
1000	600	250	1	66	28.4	NSYCRN106250P	NSYCRN106250	NSYCRN106250T	
		300	1	66	30.6	NSYCRN106300P	NSYCRN106300	NSYCRN106300T	
		800	1	66	34.5	NSYCRN108250P	NSYCRN108250	NSYCRN108250T	
		300	1	66	37.4	NSYCRN108300P	NSYCRN108300	NSYCRN108300T	
CRNG Wall-mounting steel enclosures with three-point locking system									
800	600	400	1	66	30.0	-	NSYCRNG86400	NSYCRNG86400T	
	1000	300	2	55	40.0	-	NSYCRNG810300D	-	
	1200	300	2	55	46.0	-	NSYCRNG812300D	-	
1000	600	400	1	66	36.0	-	NSYCRNG106400	NSYCRNG106400T	
	800	400	1	66	43.0	-	NSYCRNG108400	NSYCRNG108400T	
	1000	300	2 (3)	55	47.0	-	NSYCRNG1010300D	NSYCRNG1010300T	
	1200	300	2	55	55.0	-	NSYCRNG1012300D	-	
		400	2	55	60.0	-	NSYCRNG1012400D	-	
1200	600	300	1	66	37.0	-	NSYCRNG126300	NSYCRNG126300T	
		400	1	66	42.0	-	NSYCRNG126400	NSYCRNG126400T	
	800	300	1	66	45.0	-	NSYCRNG128300	NSYCRNG128300T	
		400	1	66	50.0	-	NSYCRNG128400	NSYCRNG128400T	
	1000	300	2	55	56.0	-	NSYCRNG1210300D	-	
		400	2	55	61.0	-	NSYCRNG1210400D	-	
	1200	300	2	55	64.0	-	NSYCRNG1212300D	-	
		400	2	55	90.0	-	NSYCRNG1212400D	-	
1400	1000	300	2	55	80.0	-	NSYCRNG1410300D	-	

(1) Enclosure without mounting plate.
 (2) Two cable gland plates, one on the top, one on the bottom.
 (3) Except glazed door in single door.

Selection guide

Steel wall-mounting enclosures



Mounting plate				Accessories		
Plain	Silkscreened	Microperforated	Telequick	Bakelite	DIN rails chassis	Step slides
Page 202		Page 202	Page 202	Page 203	Page 203	Page 207
NSYMM22	-	-	-	-	-	-
NSYMM32	-	NSYMF32	-	NSYMB32	-	-
NSYMM2520	-	-	-	-	-	-
NSYMM3025	-	-	NSYMR3025	NSYMB3025	-	-
NSYMM3025	-	-	NSYMR3025	NSYMB3025	-	NSYSDCR200
NSYMM33	-	NSYMF33	NSYMR33	NSYMB33	NSYMD33	-
NSYMM33	-	NSYMF33	NSYMR33	NSYMB33	NSYMD33	NSYSDCR200
NSYMM43	NSYMS43	NSYMF43	NSYMR34	NSYMB43	-	NSYSDCR200
NSYMM3045	-	-	-	NSYMB43	-	-
NSYMM43	NSYMS43	NSYMF43	NSYMR43	NSYMB43	NSYMD43	-
NSYMM43	NSYMS43	NSYMF43	NSYMR43	NSYMB43	NSYMD43	NSYSDCR200
NSYMM44	NSYMS44	NSYMF44	NSYMR44	-	-	NSYSDCR200
NSYMM64	NSYMS64	NSYMF64	NSYMR46	NSYMB64	-	NSYSDCR250
NSYMM64	NSYMS64	NSYMF64	NSYMR46	NSYMB64	-	NSYSDCR300
NSYMM54	NSYMS54	NSYMF54	NSYMR54	NSYMB54	NSYMD54	-
NSYMM54	NSYMS54	NSYMF54	NSYMR54	NSYMB54	NSYMD54	NSYSDCR200
NSYMM54	NSYMS54	NSYMF54	NSYMR54	NSYMB54	NSYMD54	NSYSDCR250
NSYMM55	NSYMS55	NSYMF55	NSYMR55	-	-	NSYSDCR250
NSYMM64	NSYMS64	NSYMF64	NSYMR64	NSYMB64	NSYMD64	-
NSYMM64	NSYMS64	NSYMF64	NSYMR64	NSYMB64	NSYMD64	NSYSDCR200
NSYMM64	NSYMS64	NSYMF64	NSYMR64	NSYMB64	NSYMD64	NSYSDCR250
NSYMM65	-	NSYMF65	NSYMR65	NSYMB65	-	-
NSYMM65	-	NSYMF65	NSYMR65	NSYMB65	-	NSYSDCR200
NSYMM65	-	NSYMF65	NSYMR65	NSYMB65	-	NSYSDCR250
NSYMM66	NSYMS66	NSYMF66	NSYMR66	-	NSYMD66	NSYSDCR200
NSYMM66	NSYMS66	NSYMF66	NSYMR66	-	NSYMD66	NSYSDCR250
NSYMM66	NSYMS66	NSYMF66	NSYMR66	-	NSYMD66	NSYSDCR300
NSYMM86	NSYMS86	NSYMF86	NSYMR86	-	-	NSYSDCR300
NSYMM75	NSYMS75	NSYMF75	NSYMR75	NSYMB75	NSYMD75	NSYSDCR200
NSYMM75	NSYMS75	NSYMF75	NSYMR75	NSYMB75	NSYMD75	NSYSDCR250
NSYMM86	NSYMS86	NSYMF86	NSYMR86	NSYMB86	NSYMD86	NSYSDCR200
NSYMM86	NSYMS86	NSYMF86	NSYMR86	NSYMB86	NSYMD86	NSYSDCR250
NSYMM86	NSYMS86	NSYMF86	NSYMR86	NSYMB86	NSYMD86	NSYSDCR300
NSYMM88	-	NSYMF88	NSYMR88	-	-	NSYSDCR200
NSYMM86	-	NSYMF88	NSYMR88	-	-	NSYSDCR300
NSYMM106	-	NSYMF106	NSYMR106	NSYMB106	-	NSYSDCR250
NSYMM106	-	NSYMF106	NSYMR106	NSYMB106	-	NSYSDCR300
NSYMM108	-	NSYMF108	NSYMR108	NSYMB108	NSYMD108	NSYSDCR250
NSYMM108	-	NSYMF108	NSYMR108	NSYMB108	NSYMD108	NSYSDCR300
NSYMM86	NSYMS86	NSYMF86	NSYMR86	NSYMB86	NSYMD86	NSYSDCR400
NSYMM108	-	NSYMF108	NSYMR810	-	-	NSYSDCR300
NSYMM128	-	NSYMF128	2 x NSYMR86*	-	-	NSYSDCR300**
NSYMM106	-	NSYMF106	NSYMR106	NSYMB106	-	NSYSDCR400
NSYMM108	-	NSYMF108	NSYMR108	NSYMB108	NSYMD108	NSYSDCR400
NSYMM1010	-	NSYMF1010	NSYMR1010 (4)	NSYMB1210	-	NSYSDCR300
NSYMM1210	-	NSYMF1210	NSYMR1012 (4)	NSYMB1210	-	NSYSDCR300**
NSYMM1210	-	NSYMF1210	NSYMR1012 (4)	-	-	NSYSDCR400**
NSYMM126	-	NSYMF126	NSYMR126	-	-	NSYSDCR300
NSYMM126	-	NSYMF126	NSYMR126	-	-	NSYSDCR400
NSYMM128	-	NSYMF128	NSYMR128	-	NSYMD128	NSYSDCR300
NSYMM128	-	NSYMF128	NSYMR128	-	NSYMD128	NSYSDCR400
NSYMM1210	-	NSYMF1210	NSYMR1210 (4)	NSYMB1210	-	NSYSDCR300
NSYMM1210	-	NSYMF1210	NSYMR1210 (4)	NSYMB1210	-	NSYSDCR400
NSYMM1212	-	2 x NSYMF126*	2 x NSYMR126*	-	-	NSYSDCR300**
NSYMM1212	-	2 x NSYMF126*	2 x NSYMR126*	-	-	NSYSDCR400**
NSYMM1410	-	-	NSYMR1410 (4)	-	-	NSYSDCR300

(4) Ref. NSYEMR mandatory.

* Order NSYCRNGSDR to mount double mounting plate.

** Except for double mounting plate, order in addition ref. NSYSDRSDCR300 (D300) or NSYSDRSDCR400 (D400).