

SIEMENS

Product data sheet

6SL3203-0CE21-0AA0


Fig. similar

 SINAMICS LINE REACTOR 380-480V 3AC 47-63HZ
 I_{LN} = 11,3A STANDALONE

Output current / rated value	11.3 A
Effective power loss	
• at 50 Hz	36 W
• at 60 Hz	39.6 W
Connectable conductor cross-section	
• for line supply conductor	2.5 mm ²
• for load-side outgoing feeder	2.5 mm ²
Design of electrical connection / for PE conductor	M4 screw
Protection class IP	IP20
Width	125 mm
Height	140 mm
Depth	71 mm
Net weight	2.1 kg

Further information

[Information and download center for Industry Automation and Drives](#)

[Technical documentation \(Motion Control\)](#)

[Industry Mall \(online ordering system\)](#)

[Service & Support \(FAQs, manuals, operating instructions, certificates, characteristics, ...\)](#)

last change:

Mar 1, 2013