



ENGLISH

Datasheet

RS Pro Braided Cable Sleeve 50mm Expandable PET 5m

RS Stock No: **408-255**



Product Details

RS Pro braided cable sleeve with a diameter of 50 mm and 5 m sleeve length, is made of expandable PET. Wires and cables can be routed through the sleeve and the flexible construction expands to accommodate a range of diameters of cable.

Features and Benefits

- Good abrasion resistance
- UV light resistant
- Resistant to most chemicals and solvents
- Flammability rating VW-1

**Specifications:**

Braided	Yes
Cable Diameter Range	45 to 73 mm
Colour	Grey
Expandable	Yes
Material	PET
Maximum Cable Diameter	73 mm
Maximum Operating Temperature	+125°C
Minimum Cable Diameter	45 mm
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +125°C
Sleeve Diameter	50 mm
Sleeve Length	5 m
Standards Met	UL 1441, RoHS Compliant