



ENGLISH

Datasheet

**RS Pro Round Fixed Height Feet, PD.3216BL 16.6mm,
PUR, +65°C -34°C**

RS Stock No: **237-287**



Product Details

RS Pro round anti-vibration feet in black colour, is made with PUR for long life durability. It has a diameter of 16.6 mm and overall height of 16.6 mm. It features excellent skid resistance with a high coefficient of friction and excellent resistance to moving and staining. It has a temperature rating of -34 to +65°C. This flexible polyurethane feet is suitable for indoor and limited outdoor applications.

Features and Benefits

- Long ageing resiliency and will not crack or harden
- Ideal for use on glass, aluminium, stainless steel, acrylic plastic, polyethylene, polystyrene, ABS, polypropylene and polycarbonate
- To ensure maximum adhesion, surfaces must be clean, dry and well unified
- Flexible polyurethane feet suitable for indoor and limited outdoor applications

**Specifications:**

| | |
|-------------------------------|------------------|
| Foot Colour | Black |
| Foot Shape | Round |
| Material | PUR |
| Mounting Type | Adhesive |
| Type | Feet |
| Diameter | 16.6 mm |
| Maximum Operating Temperature | +65°C |
| Minimum Operating Temperature | -34°C |
| Overall Height | 16.6 mm |
| Finish | Gloss |
| Hardness | 65 to 70 Shore A |