



Customer Information Sheet

DRAWING No.: M20-786XXX	SHEET 3 OF 3	IF IN DOUBT - ASK	(C)	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm
-------------------------	--------------	-------------------	-----	--------------	------------------------	----------------------



SPECIFICATION:

MATERIAL:

MOULDING = NYLON 6T UL94V-0, BLACK

CONTACTS = PHOSPHOR BRONZE

FINISH (OVER NICKEL):

42 = GOLD ON CONTACT AREA, 100% TIN ON TAILS

46 = 100% TIN

ELECTRICAL:

CURRENT RATING = 3A

VOLTAGE PROOF = 600V AC FOR 1 MINUTE

VOLTAGE PROOF = 500V AC FOR 1 MINUTE
CONTACT RESISTANCE = 20 MILLIOHMS MAX

INSULATION RESISTANCE = 1,000 MEGOHMS MIN


ENVIRONMENTAL:

TEMPERATURE RANGE = -40° TO $+105^{\circ}$

PACKING:

ACTIN
TUBE

FOR COMPLETE SPECIFICATION SEE COMPONENT SPECIFICATION C001XX (LATEST ISSUE).



ORDER CODE:

M20-786XXXX

No. OF WAYS
02 TO 40

FINISH _____
42 - SELECTIVE GOLD + 100% TIN
46 - 100% TIN

SF	4	14.07.08	10094
NAME	ISS.	DATE	C/NOTE
APPROVED: 			
CHECKED: 			
DRAWN:		S. FLOWER	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN			THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.	TOLERANCES X. = $\pm 1\text{mm}$ X.X = $\pm 0.25\text{mm}$ X.XX = $\pm 0.10\text{mm}$ X.XXX = $\pm 0.01\text{mm}$ ANGLES = $\pm 5^\circ$ UNLESS STATED	MATERIAL: SEE ABOVE	TITLE: 2.54mm PITCH SIL VERTICAL FEMALE SMT SKT ASSY DUAL ENTRY	DRAWING NUMBER: M20-786XXXX	SHT 3 OF 3
HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg						