

# Control units Ø 22 mm (fixing)

circular head, with chromium plated metal bezel

Adaptable sub-assemblies

Characteristics :  
page 5/4  
Dimensions :  
pages 5/24 and 5/25

## Operating heads for selector switches

Description	Type	Operator	Reference	Weight kg
<b>2 position</b>	stay put	Standard handle	<b>ZB2-BD2</b>	0.045
		Long handle	<b>ZB2-BJ2</b>	0.045
	1 spring return from right to left	Standard handle	<b>ZB2-BD4</b>	0.045
		Long handle	<b>ZB2-BJ4</b>	0.045
<b>3 position</b>	stay put	Standard handle	<b>ZB2-BD3</b>	0.045
		Long handle	<b>ZB2-BJ3</b>	0.045
	2 spring return to centre position	Standard handle	<b>ZB2-BD5</b>	0.045
		Long handle	<b>ZB2-BJ5</b>	0.045
	1 spring return from right to centre position	Standard handle	<b>ZB2-BD8</b>	0.045
		Long handle	<b>ZB2-BJ8</b>	0.045
	1 spring return from left to centre position	Standard handle	<b>ZB2-BD7</b>	0.045
		Long handle	<b>ZB2-BJ7</b>	0.045



ZB2-BD.



ZB2-BJ.

## Operating heads for key switches (Ronis key n° 455)

Description	Type	Key removal	Reference	Weight kg	
<b>2 position</b>	stay put	LH position	<b>ZB2-BG2</b>	0.070	
		left and RH positions	<b>ZB2-BG4</b>	0.070	
		1 spring return from right to left	LH position	<b>ZB2-BG6</b>	0.070
<b>3 position</b>	stay put	centre position	<b>ZB2-BG3</b>	0.070	
		left and RH position	<b>ZB2-BG5</b>	0.070	
		LH position	<b>ZB2-BG9</b>	0.070	
		RH position	<b>ZB2-BG09</b>	0.070	
		all 3 positions	<b>ZB2-BG0</b>	0.070	
		2 spring return to centre position	centre position	<b>ZB2-BG7</b>	0.070
		1 spring return from left to centre position	RH position	<b>ZB2-BG1</b>	0.070
		1 spring return from right to centre position	centre position	<b>ZB2-BG8</b>	0.070



ZB2-BG.

## Operating heads with black metal bezel

To order, add suffix "7" to the above references. Example : **ZB2-BD2** becomes **ZB2-BD27**.

### Other versions

Operating heads for key switches with other key numbers or other mechanical functions.  
Please consult your Regional Sales Office.