

**EK EKJB 130 T**



Sample photo

**Order symbol:** EKJB 130 T  
**Product nbr:** 2538113  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074013750  
**EI. number:**  
 Finland: 3425456  
 Electric No. Italy: 7502020  
 Electric No. Sweden: 2538113

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	280	190	130	EKJ 30-G Cover
inch:	11.0	7.5	5.1	EKJ 80-G Cover
				EKJ 30-T Cover
				EKJ 80-T Cover

**Materials:**

<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Polyamide
<b>Cover colour:</b>	Clear transparent
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Polyurethane

EKJVT	Mounting plate
EKJXT	Mounting plate isolated
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKJZR	Extension frame

**Temperatures:**

<b>Temperature °C (short term):</b>	-40 ... 120 °C
<b>Temperature °C (continuous):</b>	-40 ... 80 °C
<b>Temperature °F (short term):</b>	-40 ... 250 °F
<b>Temperature °F (continuous):</b>	-40 ... 175 °F

**Rating:**

- Ingress Protection (EN 60529): IP66/IP67
- Impact Resistance (EN 62262): IK08
- Electrical insulation: Totally insulated
- Halogen free (DIN/VDE 0472, Part 815): 1
- UV resistance: UL 508
- Flammability Rating: UL 746C 5"
- Glow Wire Test (IEC 695-2-1) °C: 960
- NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

**Accessories:**

EKJB	Base, PC
------	----------

**Certificates:**

- SGS Fimko
- Gost R

