



70 06 140

Diagonal Cutter



- the indispensable diagonal cutter for all-round use
- high quality material and precise workmanship for long service life
- precision cutting edges for soft and hard wire
- clean cutting of thin copper wires, also at the cutting-edge tips
- cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- narrow head style for use in confined areas
- Vanadium electric steel; forged, oil-hardened

Article No.	70 06 140
EAN	4003773040293
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Style	0
Head	
Insulation standard	IEC 60900 DIN EN 60900
medium hard wire Ø mm	2,5
hard wire Ø mm	1,8
soft wire Ø mm	4,0
Length mm	140
Net weight g	160



Slim head style and precise cut at blade tips:
Advantageous when working in confined areas

technical change and errors excepted

