



Product Datasheet

ENGLISH

100mm Braked Swivel Castor with White Polypropylene Wheel, 125kg load capacity



Specification	
Application	General Purpose / Industrial
Features	Ball Bearing Swivel Head
Fixing Centres	80x60mm
Fixing Centres Length	80mm
Fixing Centres Width	60mm
Fixing Hole Size	8mm
Fixing Plate Dimensions	102x84mm
Fixing Plate Length	102mm
Fixing Plate Width	84mm
Hub Bearing Type	Plain
Hub Material	Polypropylene
Load Capacity	125kg
Number of Fixing Holes	4
Overall Height	128mm
Rotation	Swivel & Brake
Tyre Material	Polypropylene
Weight Class	Light Duty
Wheel Diameter	100mm
Wheel Width	35mm