

- High-impact ABS case with non-slip grip
- Smooth wind-in mechanism
- Pocket shaped
- Ergonomical design
- Built-in bumper for smooth blade return
- With hook ring, zero point at inner side of hook ring



Type / Code No.	Packed	Blade Size		Weight g	Replacement Blade Type / Code No.
		Width	Length		
LS10CM	Carded	10 mm	10 m	250	RF10CM
LS20CM	Carded	10 mm	20 m	370	RF20CM
LS30CM	Carded	10 mm	30 m	518	RF30CM
LS10CME	Carded	10 mm / 3/8"	10 m / 33'	250	RF10CME
LS20CME	Carded	10 mm / 3/8"	20 m / 66'	370	RF20CME
LS30CME	Carded	10 mm / 3/8"	30 m / 100'	518	RF30CME

50 Footer

- Durable ABS case in Hi-Viz® orange is easy to find on the job site.
- Shock-resistant case with anti-slip covering.
- Virtually unbreakable Quad Hook, 4 rivets for extra strength.
- Lufkin roll technology permits integration of long tapes into pocket tape measures.
- Smooth running tape return
- Ergonomically shaped
- Removable belt clip
- Blade of EL15CMR is fitted with hook and ring.



Type	Code No.	Packed	Blade Size		Weight g	Shelf Pack	Replacement Blade Type	Code No.	Shelf Pack
			Width	Length					
EL15CMR	0061815014	Carded	25 mm	15 m	480	6	–	–	–

Speedwinder Tapes



- 3:1 Gear ratio for fast blade retrieval.
- Precise, easy to read black and red blade markings.
- High-impact ABS case with non-slip grip.

Type / Code No.	Packed	Blade Size		Weight g	Replacement Blade Type / Code No.
		Width	Length		
SW20CM	Carded	10 mm	20 m	422	SWR20CM
SW30CM	Carded	10 mm	30 m	530	SWR30CM
SW20CME	Carded	10 mm / 3/8"	20 m / 66'	422	SWR20CME
SW30CME	Carded	10 mm / 3/8"	30 m / 100'	530	SWR30CME

Frame Tapes



- Unique pistol grip design
- Smooth wind-in mechanism
- Compact design fits into a tool chest.
- Steel blade will not stretch.

Type / Code No.	Packed	Blade Size		Weight g	Replacement Blade Type / Code No.
		Width	Length		
FT30CM	Carded	13 mm	30 m	648	RF30CM
FT50CM	Carded	13 mm	50 m	850	RF50CM
FT30CME	Carded	13 mm / 1/2"	30 m / 100'	648	RF30CME
FT50CME	Carded	13 mm / 1/2"	50 m / 150'	850	RF50CME