

RS Part Number: **773-7998**
 Specifications and dimensions



- Boxed isolator 4 pole
- Die cast aluminium enclosure with padlockable handle

Specifications	
Height	152 mm
Width	140 mm
Depth	100 mm
Depth including switch	144 mm
Degree of protection	IP65
Rated operational current Ie AC21A	25 A
Rated operational current Ie AC22A	20 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	11 kW
Rated operational power AC3 440V	7.5 kW
Maximum gL fuse size IEC	20 A
Rated fused short circuit capacity IEC	5 kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6 mm ²
Recommended tightening torque	1.7 Nm
Number of possible auxilliary contacts	1