



Price\* : 48.30 GBP



### Main

Range	Spacial
Product name	Spacial SBM
Device application	Multi-purpose
Product or component type	Industrial box
Device short name	SBMB
Enclosure type	Bus box
Enclosure nominal height	200 mm
Enclosure nominal width	300 mm
Enclosure nominal depth	120 mm
Enclosure mounting	Wall mounted
Device composition	2 x FL21 cable gland plate 2 x cover screw 1 x glazed door 1 x DIN rail 1 x body
Body type	Single piece body folded and welded
Type of front cover	Glazed door
Cover fixing	Half turn metal screw
Lock type	Outside sealed area : PZ2 screwdriver captive screw
Removable parts	Cable gland plate, screw DIN rail, screw Cover, by captive screws

### Complementary

Material	Steel and plexiglass ( cover ) Sheet steel ( body )
Surface finish	Polyester powder
Colour	Grey ( RAL 7035 )
Standards	IEC 62208

Product certifications	BV DNV GL LR UL
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Ambient air temperature for storage	-35...60 °C
Ambient air temperature for operation	-35...80 °C
Product weight	3.346 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1241 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------