



Price\* : 28.21 GBP



### Main

Range	TeSys
Device short name	GAC0
Product or component type	Auxiliary contact block
Product compatibility	TeSys GC TeSys GY
Mounting location	Right side
Pole contact composition	1 NO + 1 NC
[Ue] rated operational voltage	250 V
[Ith] conventional free air thermal current	5 A at <= 50 °C

### Complementary

[Ui] rated insulation voltage	500 V - conforming to IEC 60947-5 500 V - conforming to VDE 0110
Mechanical durability	1 Mcycles
Connections - terminals	Screw clamp terminals cable 2.5 mm <sup>2</sup> - cable stiffness: solid Screw clamp terminals cable 2.5 mm <sup>2</sup> - cable stiffness: flexible
Tightening torque	0.8 N.m - on screw clamp terminals
Height	81 mm
Width	8.75 mm
Depth	60 mm
Product weight	0.016 kg

### Environment

Standards	IEC 60947-5
Product certifications	CEBEC NF-USE OVE

## VDE

IP degree of protection	IP20 conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m without derating

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0607 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------