



ENGLISH

Datasheet

Stock No: 413-9124

RS Pro PUR 10m Long transparent Flexible Ducting Reinforced, 13mm Bend Radius



Product Details

Flexible Ducting (Copper plated helix)

An RS Pro brand of polyurethane (PU) hosing with copper-plated steel spiral. Designed to be self-extinguishing and can be used for suction and the transport of dusts, chips and abrasive material.

Copper plated spring-steel helix between two layers of crystal clear polyurethane
Highly flexible with excellent internal and external abrasion resistance

May also be used in foundry, general industrial and agricultural applications

Temperature range -40 to +90°C

Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data



Specifications

Inner Diameter	50mm
Outer Diameter	50.8mm
Material	PUR
Length	10m
Suitable Applications	Agriculture, Foundry, Industrial
Colour	Transparent
Bend Radius	13mm
Reinforced	Yes