

CAB CAB P 604023



Sample photo

Order symbol:	CAB P 604023
Product nbr:	8104306
Description:	Polyester cabinet
Remarks:	Grey door

EAN:	6418074050038
El. number:	
Finland:	3424139
Denmark:	8212018031
Sweden:	2539823
Norway:	

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key.

Dimensions:	Length	Width	Height	Rating:
mm:	615	415	230	Ingress Protection (EN 60529): IP 66
inch:	24.2	16.3	9.1	Impact Resistance (EN 62262): IK 10
Materials:				Electrical insulation: Totally insulated
Material:	Polyester			UV resistance: UL 508
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	Polyurethane			UL Type: UL TYPE 3, 3R, 3S, 4, 4X, 12, 13
Temperatures:				Certificates:
Short term:	-50 ... 160 °C			Gost R
Continuous:	-40 ... 80 °C			
Short term:	-60 ... 320 °F			
Continuous:	-40 ... 176 °F			
Accessories:				
MP 6040	Mounting plate			
MPX 6040	Mounting Plate			
MPP 6040	Mounting Plate			
MF 6040	Mounting Frame with DIN-rails			
FP 6040-3x18	Front Plate with DIN openings			
FP 6040-D	Swing door/Front plate			
MB CAB	Swing door kit			

CAB P 615x415x230

