




POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
3	1200795103	W03000P03M020	6.56' +3.5"/2.0M +89.0MM
5	1200795110	W05000P03M020	6.56' +3.5"/2.0M +89.0MM

CONNECTOR SPECIFICATION:	
VOLTAGE RATING	3/4POL: 250V AC/DC 5POL: 60V AC/DC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP68
OPERATING TEMPERATURE	-30°C TO +80°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
ASSEMBLY IS	RoHS COMPLIANT

ITEM	COMPONENT	MATERIAL	FINISH
7	LABLE	MYLAR	BLACK/YELLOW
6	O-RING	VITON	GREEN
5	COUPLER	BRASS	NICKEL PLATED
4	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	INSERT	PUR	BLACK
2	OVERMOLD	TPE (PUR)	YELLOW
1	CABLE 0.34mm ² /22AWG (COPPER STRANDING) 3/5 CONDUCTOR	JACKET: PUR/PVC	JACKET: BLACK

FEMALE FACE VIEW	FEMALE FACE VIEW
3-POLE	5-POLE
WIRING DIAGRAM	WIRING DIAGRAM
1 BROWN 3 BLUE 4 BLACK	1 BROWN 2 WHITE 3 BLUE 4 BLACK 5 GREY

DESCRIPTION EC NO: WEU2010-0442 DRWN: REISSNER 2010/03/16 CHKD: FP APPR: FPACHER 2010/03/19	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY REISSNER	DATE 2010/03/16	MICRO-CHANGE ULTRA LOCK 3/5-POLE FEMALE STRAIGHT #22AWG PUR BLACK CABLE				
		4 PLACES	±---	±---	CHECKED BY NS	DATE 2010/03/16					
		3 PLACES	±---	±---	APPROVED BY	DATE					
		2 PLACES	±---	±.01	FPACHER	2010/03/19		MOLEX INCORPORATED			
		1 PLACE ±0.3			ANGULAR ± --- °		MATERIAL NO.	SEE TABLE	DOCUMENT NO.	SD-120079-043	SHEET NO. 1 OF 1
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
1	REV										