



ENGLISH

Datasheet

Stock No: 236-284

RS Pro Incandescent Beacon, Rotating, Surface Mount, 12 V dc, 24 V dc



Product Details

Rotating Filament Beacons

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.

- High protection rating of IP56
- Magnetic version is rated to 70mph
- Optional cage guard for three-point mounting versions
- Surge protection for safety against peak voltage
- Full internal suppression for maximum interference reduction
- 166mm diameter footprint
- 125 rotations per minute

Note

Lens must be purchased separately

Supplied with

Appropriate SES (E14) 60W bulb (except the 12/24V versions, which are not supplied with a bulb)

Filament



ENGLISH

Specifications

Supply Voltage	12 V dc, 24 V dc
Light Effect	Rotating
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Incandescent
Current Type	DC
Base Diameter	166mm
Housing Colour	Black
Series	V10993
Height	207mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C