





SPECIFICATIONS	
CONTACT CARRIER MATERIAL/COLOR	PBT OR NYLON/GRAY
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
GASKET	PERBUNAN OR FLUOR RUBBER
RATED CURRENT [A]	8.0 A
RATED VOLTAGE [V]	150 V
MAX. CONDUCTORS SIZE	18 AWG
TERMINATION METHOD	SOLDER
TEMPERATURE	−40°C to +125°C (−40°F to +257°F)
PROTECTION CLASS	IEC IP 65
CABLE DIAMETERS	10mm (.394") to 14mm (.551)



NOTE
PRELIMINARY
SPECIFICATIONS

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:
1. THE CABLE GLAND IS PG 13.5 CABLE GLAND.

NOTES: 1. THE CABLE GLAND IS PG 13.5 CABLE GLAND.					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. 		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com TURCK INC High Technology Sensors and Automation Controls					
					MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY				DRFT		RDS		DATE 03/02/11	
									DSGN		SCALE 1 = 1.0					
					FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT MILLIMETER [INCH]				IDENTIFICATION NO. U4574-5			
DO NOT SCALE THIS DRAWING				FILE: U4574-5					SHEET 1 OF 1							
P1		RDS	03/02/11													
REV	DESCRIPTION	BY	DATE	ECO NO.												