



ENGLISH

Datasheet

On/Off Temperature Controller, 72 x 72mm, PT100 Input, 230 V ac Supply, 0 → +400°C Measurement Range

RS Stock number [798-3463](#)



Analogue Set, ON / OFF or Time Proportional Digital & Analogue Temperature Controller

- 4 Digits Display
- J type Thermocouple Input or ,
K type Thermocouple Input or ,
R type Thermocouple Input or ,
S type Thermocouple Input or ,
2 or 3-wire PT 100 Input (It must be determined in order)
- ON/OFF or Time Proportional Operation
- Adjustable Hysteresis Value with DIP Switch for ON/OFF Control
- Adjustable Control Period with DIP Switch for ON/OFF Control
- Adjustable Set Offset Value

Specifications

To find a similar product, based on selected attributes, click the green button

Input Type	PT100
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	0°C
Panel Depth	76mm
Size	72 x 72mm
Supply Voltage	230 V ac