



ENGLISH

Datasheet

RS Pro IP66 Wall Box, 304 Stainless Steel, 360 x 360 x 150mm

RS Stock No: **749-7010**



Product Details

RS Pro IP66 wall box measuring 360 x 360 x 150 mm, is made of 304 stainless steel. It is available in a variety of sizes.

Features and Benefits

- Enclosure material SUS304 1.2 mm stainless steel
- Stainless steel quarter turn lock and 180° hinge
- Interior and mounting plate are finished with heat fused polyester powder
- Double - bit key
- Earth stud

**Specifications:**

Application	Industrial, Electrical, Electronic
Body Material	304 Stainless Steel
Chassis Plate	Yes
Colour	Natural
Door Lock Type	Single Quarter Turn
External Depth	150 mm
External Dimensions	360 x 360 x150 mm
External Height	360 mm
External Mounting Type	Wall
External Width	360 mm
Fixing Kit	No
Gland Plate	No
IP Rating	IP66
Special Features	180° Hinge, Double Bit Key
Standards Met	RoHS Compliant
Transparent Door	No