



Sample photo

Order symbol: ALN 232811
Product nbr: 7811370
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016188
EI. number:
Finland: 3420037
Electric No. Sweden: 2536337

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	280	230	110	ARH 2328	DIN-35 Mounting rail
inch:	11.0	9.1	4.3	MRS 28541	Wall fastening lug (2 pcs)
				PH A & AH A/B	Hinge set
Materials:				Rating:	
Material:	Aluminium			Ingress Protection (EN 60529): IP66/IP67/IP68	
Base colour:	RAL 7001			Impact Resistance (EN 62262): IK08	
Cover screws material:	Stainless steel			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Cover colour:	RAL 7001				
Temperatures:					
Temperature °C (short term):	-50 ... 140 °C				
Temperature °C (continuous):	-50 ... 80 °C				
Temperature °F (short term):	-60 ... 285 °F				
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:					
AM 2328	Mounting plate				

