

Datasheet

RS Pro 3.5A Axial FF Non-Resettable Wire Ended Fuse, 250 V ac

RS Stock No: **764-9592**



Product Details

RS Pro axial non-resettable fuse withstands currents up to 3.5 A. This wire-ended fuse offers FF speed with a voltage rating of 250 V ac. It has epoxy-coated body for added durability. The very fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- FF speed fuse
- Non-resettable
- Axial
- Wire-ended

**Specifications:**

Body Diameter	3.18 mm
Body Height	7.1 mm
Body Material	Epoxy Coated
Breaking Capacity (at Maximum Voltage Rating)	50 A at 250 V ac
Current Rating	3.5 A
Fuse Speed	FF
Lead Orientation	Axial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	250 V ac
Voltage Rating	250 V ac
Wire Diameter	0.64 mm
Wire Length	28 mm
Fuse Type	Very Fast Acting
Standards Met	TUV, PSE, RoHS