

Datasheet

RS Pro Fixed Height Feet, 02540021010 20mm, 2mm, Polychloroprene Rubber, +90°C -30°C

RS Stock No: **136-7679**



Product Details

RS Pro anti-vibration feet in black colour, has polychloroprene rubber construction for long life durability. This HELAVIA series anti-vibration feet has a diameter of 20 mm and overall height of 4.5 mm. It features a temperature rating of -30 to +90°C.

Features and Benefits

- It is made with polychloroprene rubber material
- Temperature ranges between -30 to +90°C
- Comes in black colour



Specifications:

Foot Colour	Black
Material	Polychloroprene Rubber
Type	Feet
Diameter	20 mm
Foot Height	2 mm
Maximum Operating Temperature	+90°C
Minimum Operating Temperature	-30°C
Overall Height	4.5 mm